Product data sheet

Specifications





Illuminated selector switch, Harmony 9001SK, plastic, long handle, green, 30mm, 3 positions, stay put, 110-120V, screw terminals for lug, 1 C/O

9001SK43J1FGH13Y238

Product availability: Stock - Normally stocked in distribution facility

Price*: 231.00 USD

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Illuminated selector switch
Device Short Name	9001SK

Complementary

Complementary	
Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Net Weight	0.54 lb(US) (0.245 kg)
Operator Position Information	3 positions
Contacts Type And Composition	1 C/O
Device Presentation	Complete product
Cap/Operator Or Lens Colour	Green
[Us] Rated Supply Voltage	110120 V
Light Block Supply	Via integral transformer
Operator Profile	Long handle
Type Of Operator	Stay put
Supply Frequency	5060 Hz
Size	30 mm
Bulb Base	BA 9s
Light Source	Incandescent bulb
Connections - Terminals	Screw terminals for lug
Cam Profile	3

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class II IEC 61140

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product Certifications	CE CSA LR24590 class 3211 03 UL listed file E42259 CCN NKCR

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
Gtin	00785901348191
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free

Yes

Rohs Exemption Information

Certifications & Standards

REACh Declaration
Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS declaration
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov