Product data sheet

Specifications

SQUARE D





30mm push button, Type SK, illuminated selector switch, 3 position, 120VAC light module, green knob, no contacts, NEMA 4, 4X

9001SK43J1G

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 167.00 USD

Main

Product Or Component Type	Head for illuminated selector switch
Device Short Name	К
Enclosure Type	Dust and oil resistant weatherproof enclosure indoor/outdoor
Mounting Diameter	1.18 in (30 mm)
Range Of Product	Harmony 9001SK

Complementary

· · · · · · · · · · · · · · · · · · ·	
Bezel Material	Plastic
Bulb Base	BA 9s
Contacts Type And Composition	Without contact block
Light Block Supply	Via transformer 120 V AC 50/60 Hz Via transformer 110 V AC 50/60 Hz
Operator Position Information	3 positions
Operator Profile	Standard handle
Operator Profile	1 projecting push-button
Size	30 mm
Type Of Operator	Maintained
Cap/Operator Or Lens Colour	Green
[Us] Rated Supply Voltage	110120 V
Light Block Supply	Via integral transformer
Type Of Operator	Stay put
Contacts Type And Composition	Without contact block

Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product Certifications	CE CSA LR24590 class 3211 03 UL listed file E42259 CCN NKCR

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901960089
Returnability	No
Country Of Origin	MX

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	6.40 oz (181.437 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free

Yes

Rohs Exemption Information

Certifications & Standards

REACh Declaration
Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS declaration
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov