



Price** : 167.00 USD

9001SK44J1R has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

Range of product	Harmony 9001SK
Product or component type	Selector switch
Device short name	9001SK
Type of operator	Maintained
Operator profile	Standard knob red

Complementary

Bezel material	Plastic
Mounting diameter	1.18 in (30 mm)
Product weight	0.13 lb(US) (0.059 kg)
Shape of signaling unit head	Round
Operator position information	3 positions
Contacts type and composition	Without contact block
Mechanical durability	500000 cycles
Light block supply	Via integral transformer
Light source	Incandescent
Bulb base	BA 9s
[Us] rated supply voltage	110...120 V AC 50/60 Hz
Compatibility code	9001SK

Environment

Protective treatment	TC
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 1

NEMA 12
NEMA 13
NEMA 2
NEMA 3
NEMA 3R
NEMA 4
NEMA 4X
NEMA 6

Standards	EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C 4520 JIS C 852 UL 508 CSA C22.2 No 14
Product certifications	NEMA UL 508
Vibration resistance	7 gn (f = 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27

Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------