Product data sheet

Specifications





30mm Push Button, Type SK, pilot light, transformer, 120 VAC, green fresnel cap

9001SKP1G31

Product availability: Stock - Normally stocked in distribution facility

Price*: 153.00 USD

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Pilot light
Lens Type	Fresnel plastic
Light Block Supply	Via transformer 120 V AC 50/60 Hz Via integral transformer 110 V AC 50/60 Hz

Complementary

Complementary	
Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	Green
Light Source	incandescent
Bulb Base	BA 9s
[Us] Rated Supply Voltage	110120 V AC
Operating Position	Any position
Operating Mode	Normal
Cad Overall Width	2.13 in (54 mm)
Cad Overall Height	2.76 in (70 mm)
Cad Overall Depth	1.65 in (42 mm)
Device Presentation	Complete product
Lens Type	Fresnel
[Us] Rated Supply Voltage	110120 V
Light Block Supply	Via integral transformer
Supply Frequency	5060 Hz
Lens Material	Polycarbonate
Size	30 mm
Light Source	Incandescent bulb

Environment

Protective Treatment	тс
Ip Degree Of Protection	IP66

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901959731
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	2.20 in (5.588 cm)
Package 1 Length	3.70 in (9.398 cm)
Package 1 Weight	5.92 oz (167.829 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

REACh Declaration
Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS declaration
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
End of Life Information
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov