

# Product data sheet

Specifications

SQUARE D



Illuminated push-button head,  
Harmony 9001SK, plastic,  
mushroom 41mm, red, 30mm, 3  
positions, return to center,  
110-120V

9001SKR8P1R

Product availability: Non-Stock - Not normally stocked in  
distribution facility

Price\*: 201.00 USD

## Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for illuminated push-button
Device Short Name	9001SK
Operator Additional Information	Screw-on plastic

## Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Contacts Type And Composition	Without contact block
Mechanical Durability	5000000 cycles
Device Presentation	Basic element
Cap/Operator Or Lens Colour	Red
[Us] Rated Supply Voltage	110...120 V
Light Block Supply	Via integral transformer
Operator Profile	Mushroom Ø 41 mm
Type Of Operator	Pull : spring return, center : stay put, push : spring return
Operator Position Information	3 positions
Supply Frequency	50...60 Hz
Size	30 mm
Bulb Base	BA 9s
Light Source	Incandescent bulb

## Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-5-1 CSA C22.2 No 14 JIS C 852 EN/IEC 60947-5-4 UL 508 JIS C 4520
Ip Degree Of Protection	IP66

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13
---------------------------	----------------------------

## Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901042983
Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.08 in (12.903 cm)
Package 1 Width	2.00 in (5.08 cm)
Package 1 Length	12.90 in (32.774 cm)
Package 1 Weight	6.40 oz (181.437 g)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Reach Free Of Svhc	
 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>