

9001SKR9YH8

PUSHBUTTON 600VAC 10AMP 30MM SK +OPTIONS



Price* : 188.00 USD

9001SKR9YH8 has not been replaced. Please contact your customer care center for more information.



⚠ Discontinued

Main

Bezel material	Black plastic
Device short name	SK
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor Enclosure corrosion resistance indoor/outdoor
Light source	Without
Mounting diameter	1.18 in (30 mm)
Operator additional information	Without guard Screw-on plastic mushroom 1.63 in

Complementary

Line Rated Current	10 A
Cap/Operator or lens colour	Yellow
Contact operation	Standard fingersafe
Contacts type and composition	2 NC
Control type	Push-button
Electrical connection	Screw clamp terminal
Light block supply	Without supply
Marking	Unmarked
Mounting support	Panel
Operator position information	2 positions
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Type of operator	Maintained
Utilisation category	AC-15 DC-13

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------