

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 81.00 USD



### Main

Bezel material	Black plastic
Device short name	K
Enclosure type	Dust and oil resistant weatherproof enclosure indoor/outdoor Corrosion resistance enclosure indoor/outdoor
Mounting diameter	1.18 in (30 mm)

### Complementary

Cap/Operator or lens colour	Black
Contacts type and composition	Without contact block
Control type	Push-button
Mounting support	Panel
Operator position information	2 positions
Operator profile	Gloved hand knob
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Type of operator	Left to right spring return

### Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

### Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1

GTIN	00785901398738
Nbr. of units in pkg.	1
Package weight(Lbs)	0.20000000000000001
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------