

Product availability : Stock - Normally stocked in distribution facility



Price\* : 106.00 USD



### Main

Range of product	Harmony 9001SK
Product or component type	Selector switch
Device short name	9001SK

### Complementary

Bezel material	Plastic
Mounting diameter	1.18 in (30 mm)
Device presentation	Complete product

### Environment

Protective treatment	TC
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

### Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901043713
Nbr. of units in pkg.	1
Package weight(Lbs)	0.19
Returnability	Y

Country of origin	MX
-------------------	----

**Offer Sustainability**

RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------