



Price\* : 184.00 USD



9001SKS57BH2 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

### Main

Bezel material	Black plastic
Device short name	SK
Enclosure type	Weatherproof enclosure dust and oil resistant indoor/outdoor Enclosure corrosion resistance indoor/outdoor
Mounting diameter	1.18 in (30 mm)

### Complementary

Line Rated Current	10 A
Cap/Operator or lens colour	Black
Contact operation	Standard fingersafe
Contacts type and composition	2 NO + 2 NC
Control type	Push-button
Electrical connection	Screw clamp terminal
Mounting support	Panel
Operator position information	3 positions
Operator profile	Standard knob
Operator profile	1 projecting push-button
Permissible voltage	<= 600 V
Shape	Round head
Type of operator	Spring return both sides to centre
Utilisation category	DC-13 AC-15

### Environment

NEMA degree of protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product certifications	UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE

Ordering and shipping details

Category	21429 - 9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901806172
Nbr. of units in pkg.	1
Package weight(Lbs)	0.20000000000000001
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------