





Selector switch head, Harmony 9001SK, plastic, without handle, 30mm, 3 positions, spring return left to center

9001SKS6

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 97.50 USD

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for selector switch
Device Short Name	9001SK
Type Of Operator	Left to centre spring return

Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Net Weight	0.13 lb(US) (0.059 kg)
Shape Of Signaling Unit Head	Round
Operator Position Information	3 positions
Contacts Type And Composition	Without contact block
Mechanical Durability	500000 cycles
Device Presentation	Basic element
Operator Profile	Without handle
Type Of Operator	Spring return
Size	30 mm
Return	Left to centre
Cam Profile	0

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
	NEMA 4X
	NEMA 6
Standards	UL 508
	JIS C 852
	CSA C22.2 No 14
	EN/IEC 60947-1
	EN/IEC 60947-5-1
	EN/IEC 60947-5-4
	JIS C 4520
Product Certifications	NEMA
	UL 508
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 an IEC 60068-2-27

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901779858
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.62 in (19.355 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	19.35 in (49.161 cm)
Package 1 Weight	2.08 oz (58.967 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov