# Product data sheet

Specifications





Selector switch head, Harmony 9001SK, plastic, standard handle, black, 30mm, 3 positions, spring return left to center

9001SKS63B

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 81.00 USD

#### Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for selector switch
Device Short Name	9001SK

#### Complementary

Complementary	
Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Operator Position Information	3 positions
Contacts Type And Composition	Without contact block
Device Presentation	Basic element
Cap/Operator Or Lens Colour	Black
Operator Profile	Standard handle
Type Of Operator	Spring return
Size	30 mm
Return	Left to centre
Cam Profile	3

### Environment

Protective Treatment	тс
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product Certifications	CSA LR24590 class 3211 03 CE UL listed file E42259 CCN NKCR

## Ordering and shipping details

Category

US10CS121429

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Discount Schedule	0CS1
Gtin	785901044109
Returnability	Yes
Country Of Origin	МХ

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.81 in (4.600 cm)
Package 1 Width	2.17 in (5.500 cm)
Package 1 Length	3.90 in (9.900 cm)
Package 1 Weight	2.08 oz (59.000 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	14
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	2.26 lb(US) (1.026 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	448
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	90.02 lb(US) (40.832 kg)

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov