





Selector switch head, Harmony 9001SK, plastic, long handle, black, 30mm, 3 positions, spring return right to center

9001SKS72FB

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 121.50 USD

Main

| Product Or Component Type | Head for selector switch |
|---------------------------|--|
| Device Short Name | К |
| Enclosure Type | Dust and oil resistant weatherproof enclosure indoor/outdoor |
| Mounting Diameter | 1.18 in (30 mm) |
| Range Of Product | Harmony 9001SK |

Complementary

| Bezel Material | Plastic |
|-------------------------------|-------------------------------|
| Cap/Operator Or Lens Colour | black |
| Contacts Type And Composition | Without contact block |
| Operator Position Information | 3 positions |
| Operator Profile | Long handle |
| Operator Profile | 1 projecting push-button |
| Size | 30 mm |
| Type Of Operator | Spring return right to centre |
| Cap/Operator Or Lens Colour | Black |
| Type Of Operator | Spring return |
| Contacts Type And Composition | Without contact block |

Environment

| Nema Degree Of Protection | NEMA 1/2/3/3R/4/4X/6/12/13 |
|---------------------------|---|
| Product Certifications | CSA LR24590 class 3211 03 UL listed file E42259 CCN NKCR CE |

Ordering and shipping details

| Category | US10CS121429 |
|-------------------|--------------|
| Discount Schedule | 0CS1 |
| Gtin | 785901044208 |
| Returnability | No |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 7.62 in (19.355 cm) |
| Package 1 Width | 3.00 in (7.62 cm) |
| Package 1 Length | 19.35 in (49.161 cm) |
| Package 1 Weight | 2.08 oz (58.967 g) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |