

# Product data sheet

Specifications

SQUARE D



## SELECTOR SWITCH 600VAC 10A 30MM SK

9001SKS88BH11

 Discontinued on: Oct 11, 2019

 Discontinued

### Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Selector switch
Device Short Name	9001SK
Type Of Operator	stay put
Operator Profile	Black standard knob

### Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Operator Position Information	4 positions
Contacts Type And Composition	3 C/O
Product Compatibility	9001KA1 side 1 and 2
Device Presentation	Complete product

### Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product Certifications	CSA LR24590 class 3211 03 UL listed file E42259 CCN NKCR CE

### Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

### Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months