# **Product data sheet**

Specification





Push-to-test pilot light head, Harmony 9001SK, plastic, without cap, 30mm, 110...120V

9001SKT1

Product availability: Stock - Normally stocked in distribution facility

Price\*: 185.00 USD

### Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for push-to-test pilot light
Light Block Supply	Via transformer 110 V AC 50/60 Hz Via transformer 120 V AC 50/60 Hz

### Complementary

Bezel Material	Plastic	
Mounting Diameter	1.18 in (30 mm)	
Shape Of Signaling Unit Head	Round	
Cap/Operator Or Lens Colour	Without cap	
Bulb Base	BA 9s	
Operating Mode	Push-to-test	
[Us] Rated Supply Voltage	110120 V	
Light Block Supply	Via integral transformer	
Contacts Type And Composition	1 C/O	
Supply Frequency	5060 Hz	
Size	30 mm	
Light Source	Incandescent bulb	

#### **Environment**

Protective Treatment	TC	
Ip Degree Of Protection	IP66	

### Ordering and shipping details

Category	US10CS121429	
Discount Schedule	0CS1	
Gtin	785901513582	
Returnability	Yes	
Country Of Origin	MX	

### **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	2.00 in (5.080 cm)	
Package 1 Width	2.20 in (5.588 cm)	
Package 1 Length	4.50 in (11.430 cm)	
Package 1 Weight	7.20 oz (204.100 g)	
Unit Type Of Package 2	S01	
Number Of Units In Package 2	14	
Package 2 Height	5.91 in (15 cm)	
Package 2 Width	5.91 in (15 cm)	
Package 2 Length	15.75 in (40 cm)	
Package 2 Weight	6.74 lb(US) (3.057 kg)	
Unit Type Of Package 3	P06	
Number Of Units In Package 3	448	
Package 3 Height	29.53 in (75.000 cm)	
Package 3 Width	31.50 in (80.000 cm)	
Package 3 Length	23.62 in (60.000 cm)	
Package 3 Weight	233.33 lb(US) (105.837 kg)	

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
	Mercury Free	
<b>9</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	