### Product data sheet

Specifications





# Push-to-test pilot light, Harmony 9001SK, plastic, polycarbonate, fresnel, white, 30mm, 110-120V

9001SKT1W31

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 295.50 USD

#### Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Push-to-test pilot light
Lens Type	Fresnel plastic
Light Block Supply	Via transformer 110 V AC 50/60 Hz Via transformer 120 V AC 50/60 Hz

#### Complementary

Complementary	
Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	White
Bulb Base	BA 9s
Operating Mode	Push-to-test
Lens Type	Fresnel
[Us] Rated Supply Voltage	110120 V
Light Block Supply	Via integral transformer
Contacts Type And Composition	1 C/O
Supply Frequency	5060 Hz
Lens Material	Polycarbonate
Size	30 mm
Light Source	Incandescent bulb

## Environment Protective Treatment TC Ip Degree Of Protection IP66

#### Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901044437
Returnability	Yes

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

#### **Packing Units**

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.35 in (16.129 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	16.13 in (40.968 cm)
Package 1 Weight	7.20 oz (204.117 g)

#### **Contractual warranty**

Warranty

18 months

#### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

REACh Declaration
Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China RoHS declaration
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
End of Life Information
WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov