

Product data sheet

Specifications

SQUARE D



PILOT LIGHT 120VAC 30MM SK +OPTIONS

9001SKT1W6

Discontinued on: Oct 11, 2019

Discontinued

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Pilot light
Device Short Name	9001SK
Lens Type	Domed glass
Light Block Supply	Via integral transformer 110...120 V AC 50/60 Hz 6 V)

Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	White
Light Source	incandescent
Bulb Base	BA 9s
[Us] Rated Supply Voltage	110...120 V AC 50/60 Hz
Tightening Torque	7.08 lbf.in (0.8 N.m) EN/IEC 60947-1
Shape Of Screw Head	Cross slotted
Connections - Terminals	Screw clamp terminals, 1 x 0.22...2 x 1.5 mm² EN/IEC 60947-1
[Ith] Conventional Free Air Thermal Current	10 A
Short-Circuit Protection	10 A cartridge fuse EN/IEC 60947-5-1
[Ui] Rated Insulation Voltage	250 V 2)EN/IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	2.5 kV EN/IEC 60947-1
Operating Position	Any position
Operating Mode	Push-to-test
Cad Overall Width	2.13 in (54 mm)
Cad Overall Height	2.76 in (70 mm)
Cad Overall Depth	1.65 in (42 mm)
Net Weight	0.40 lb(US) (0.181 kg)

Environment

Electrical Shock Protection Class	Class II IEC 61140
-----------------------------------	--------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective Treatment	TC
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X
Vibration Resistance	7 gn 2...500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Standards	UL 508 JIS C8201-5-1 EN/IEC 60947-1 EN/IEC 60947-5-4 JIS C 852 CSA C22.2 No 14 EN/IEC 60947-5-1 JIS C8201-1
Product Certifications	NEMA UL 508

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
Gtin	00785901841517
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------