





PILOT LIGHT 120V 30MM SK +OPTIONS

9001SKT38L31

Discontinued on: Jan 23, 2021



Main

Range Of Product	Harmony 9001SK	
Product Or Component Type	Pilot light	
Device Short Name	9001SK	
Lens Type	Fresnel plastic	
Light Block Supply	Direct 120 V AC/DC	

Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Round
Cap/Operator Or Lens Colour	Blue
Light Source	incandescent
Bulb Base	BA 9s
[Us] Rated Supply Voltage	120 V AC/DC
Tightening Torque	7.08 lbf.in (0.8 N.m) EN/IEC 60947-1
Shape Of Screw Head	Cross slotted
Connections - Terminals	Screw clamp terminals, 1 x 0.222 x 1.5 mm² EN/IEC 60947-1
[Ith] Conventional Free Air Thermal Current	10 A
Short-Circuit Protection	10 A cartridge fuse EN/IEC 60947-5-1
[Ui] Rated Insulation Voltage	250 V 2)EN/IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	2.5 kV EN/IEC 60947-1
Operating Position	Any position
Operating Mode	Push-to-test
Cad Overall Width	2.13 in (54 mm)
Cad Overall Height	2.76 in (70 mm)
Cad Overall Depth	1.65 in (42 mm)
Net Weight	0.40 lb(US) (0.181 kg)

Environment

Electrical Shock Protection Class Class II IEC 61140

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Protective Treatment	TC
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3 NEMA 4 NEMA 4
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Standards	EN/IEC 60947-5-4 JIS C8201-5-1 EN/IEC 60947-1 EN/IEC 60947-5-1 CSA C22.2 No 14 UL 508 JIS C 852 JIS C8201-1
Product Certifications	UL 508 NEMA

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
Gtin	00785901415572
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov