



Price\*\* : 372.00 USD



9001SKY206 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

### Main

Range of product	Harmony 9001KY
Product or component type	Control station
Device short name	9001KY
Provided equipment	Label plate OPEN-CLOSE
Contact block name	KA1
Product specific application	For hoisting and mechanical handling applications
Level or class	Class II Division 2 Group G Class III

### Complementary

Enclosure/Cubicle description	Wall-mounted enclosure 2 cut-outs Ø 30 mm
Enclosure material	Polymeric
Type of installation	Indoor/outdoor
Control station composition	2 push-buttons 2 NO + 2 NC
Mechanical interlocking	Without mechanical interlock
Connector type	Screw clamp connector
Connections - terminals	Direct connection AWG 2) solid stranded Direct connection AWG 12) solid stranded Direct connection AWG 24) solid stranded
[Ue] rated operational voltage	600 V
[Ie] rated operational current AC	10 A

### Environment

NEMA degree of protection	NEMA 13 NEMA 4 NEMA 1 NEMA 3
Environmental characteristic	Dust and oil resistant Resistant against immersion in water
Product certifications	UL listed

Ambient air temperature for operation	-13...140 °F (-25...60 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)

### Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
GTIN	00785901713722
Package weight(Lbs)	32.00 oz (907.185 g)
Returnability	No
Country of origin	MX

### Contractual warranty

Warranty	18 months
----------	-----------