Specifications



Foot Switch, Harmony, industrial, unshielded, maintained contact, 3A at 230 VAC, SPST contact, NEMA 2, 4, 13 enclosure

9002AW11

Product availability: Stock - Normally stocked in distribution facility

Price*: 575.00 USD

Λ.Λ	~	5
IVI	a	In

Range	9002AW
Product	Foot switch
Contact Operation	1 step
Certifications	CSA UL Listed
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	SPST
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Unshielded
Operator Action	Maintained
Rated Breaking Capacity	 6 A 115 V AC inductive control circuit UL 508 3 A 230 V AC inductive control circuit UL 508 2.2 A 125 V DC inductive control circuit UL 508 2.2 A 125 V DC resistive control circuit UL 508 1.1 A 250 V DC inductive control circuit UL 508 1.1 A 250 V DC resistive control circuit UL 508
Height	3.90 in (99 mm)
Width	4.49 in (114 mm)
Depth	8.50 in (216 mm)

Ordering and shipping details

Category	US10CS121441
Discount Schedule	0CS1
Gtin	785901816737
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.39 in (8.6 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Width	5.00 in (12.7 cm)
Package 1 Length	9.49 in (24.1 cm)
Package 1 Weight	3.00 lb(US) (1.36 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov