





Foot Switch, Harmony 9002AW, industrial, pedal and side shields, SPDT contact, NEMA 2, 4, 13 enclosure, 5A resistive at 600V AC

9002AW2

Product availability: Stock - Normally stocked in distribution facility

Price\*: 363.00 USD

#### Main

Range	9002AW	
Product	Foot switch	
Contact Operation	1 step	
Certifications	UL Listed CSA	
Cable Entry	0.75 inch NPT conduit entrance	
Contact Arrangement	SPDT	
Enclosure Rating	NEMA 2/4/13	
Voltage Rating	600 V AC/DC	
Protection	Pedal shield Side shield	
Operator Action	Spring return	
Rated Breaking Capacity	15 A 120 V AC inductive control circuit UL 508 10 A 240 V AC inductive control circuit UL 508 6 A 480 V AC inductive control circuit UL 508 5 A 600 V AC inductive control circuit UL 508 15 A 120 V AC resistive control circuit UL 508 0.5 A 125 V DC resistive control circuit UL 508	
Height	4.84 in (123 mm)	
Width	5.39 in (137 mm)	
Depth	9.02 in (229 mm)	

## Ordering and shipping details

Category	US10CS121441	
Discount Schedule	0CS1	
Gtin	785901815921	
Returnability	Yes	
Country Of Origin	MX	

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	5.80 in (14.732 cm)	
Package 1 Width	5.60 in (14.224 cm)	
Package 1 Length	12.00 in (30.48 cm)	
Package 1 Weight	4.64 lb(US) (2.105 kg)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	72	
Package 2 Height	40.00 in (101.6 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	335.00 lb(US) (151.953 kg)	

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov