

Product availability : Stock - Normally stocked in distribution facility



Price* : 65.00 USD



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch head
Device short name	9007C
Head type	Rotary head
Product compatibility	9007C
Associated lever	9007C
Associated body	9007C
Movement of operating head	Rotary
Type of operator	Zinc spring return without operating lever (low differential)
Type of approach	1 or 2 programmable direction lateral approach
Positive opening	Without

Complementary

Switch actuation	From left and right CW and CCW
Product weight	0.41 lb(US)

Environment

Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901500889

Nbr. of units in pkg.	1
Package weight(Lbs)	0.41000000000000003
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1150 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------