

9007AP304

9007 snap switch - cross roller plunger operator - bushing mount

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 61.00 USD



9007AP304 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

Main

Range of product	9007
Series name	Heavy duty
Product or component type	Snap limit switch operator
Device short name	9007AO/CO

Complementary

Operator profile	Plunger head
Fixing mode	By the head
Movement of operating head	Linear
Product compatibility	Snap basic limit switch
Type of operator	Steel spring return cross roller plunger
Switch actuation	By 30° cam
Type of approach	2 directions traverse approach
Width	0.83 in
Height	2.5 in
Depth	1.6 in
Product weight	0.1 lb(US)

Environment

NEMA degree of protection	NEMA 1 Nema type 250
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F

Ordering and shipping details

Category	21491 - 9007 A SNAP SWITCHES
----------	------------------------------

Discount Schedule	DS1
GTIN	00785901348238
Nbr. of units in pkg.	1
Package weight(Lbs)	0.10000000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------