

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 308.00 USD



Main

Body type	Plug-in
Device short name	AW
Head type	Top plunger head
Series name	Heavy duty

Complementary

Line Rated Current	15 A
Body material	Cast zinc
Contact operation	Snap action
Fluid connection type	0.5 inch BSP conduit entrance
Impregnation material	Oil
Material	Iron roller
Operating distance	0.19...0.31 inch
Operating travel	0.05 in 0.09 in
Size	0.63 x 0.25 inch roller
Switch actuation	Horizontal
Torque value	3 lbf.in
Type of operator	Momentary Spring return roller

Environment

Ambient air temperature for operation	0...185 °F
NEMA degree of protection	NEMA 1/2/4/12/13
Product certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Ordering and shipping details

Category	21496 - 9007 AW PRECISION LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901419082
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------