

# Product data sheet

## Characteristics

# 9007B21

## 9007T/FT limit switch lever - zinc - fixed length - no roller - user supplied

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 50.00 USD



### Main

|                             |   |
|-----------------------------|---|
| Range of product            | 9007  |
| Series name                 | Severe duty   |
| Product or component type   | Limit switch lever  |
| Device short name           | 9007T/FT  |
| Associated head             | 9007AS9<br>9007BS9<br>9007CS9<br>9007NS9<br>9007T10S9<br>9007T5S9                 |
| Associated complete product | 9007T<br>9007FT<br>9007C..S9  |
| Movement of operating head  | Rotary  |
| Type of operator            | Cast zinc spring return roller lever without roller length: 2.88 in - offset: - - |
| Type of approach            | Lateral approach  |
| Positive opening            | Without   |

### Complementary

|                  |            |
|------------------|------------|
| Switch actuation | By 30° cam |
| Product weight   | 0.1 lb(US) |

### Environment

|                                       |                      |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -10...185 °F         |
| Ambient air temperature for storage   | -10...185 °F         |
| Environmental characteristic          | Standard environment |

## Ordering and shipping details

|                       |                            |
|-----------------------|----------------------------|
| Category              | 21494 - 9007 ARMS FOR FT,T |
| Discount Schedule     | DS1                        |
| GTIN                  | 00785901888000             |
| Nbr. of units in pkg. | 1                          |
| Package weight(Lbs)   | 0.10000000000000001        |
| Returnability         | N                          |
| Country of origin     | MX                         |

## Offer Sustainability

|                                  |  |
|----------------------------------|--|
| RoHS (date code: YYWW)           | Will not be compliant<br>Will not be compliant   |
| REACH                            | Reference not containing SVHC above the threshold<br>Reference not containing SVHC above the threshold                     |
| Product environmental profile    | Available  |
| Product end of life instructions | Need no specific recycling operations  |
| California proposition 65        | WARNING: This product can expose you to chemicals including:   |
| ----- Substance 1                | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and                                |
| ----- Substance 2                | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. |
| ----- More information           | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                              |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|