

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 50.00 USD



Main

Range of product	9007
Series name	Severe duty
Product or component type	Limit switch lever
Device short name	9007T/FT
Associated head	9007AS9 9007BS9 9007CS9 9007NS9 9007T10S9 9007T5S9
Associated complete product	9007T 9007FT 9007C..S9
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 2.5 in - offset: - convertible rollers, 2 on same side
Type of roller	2 steel outside roller (convertible) diameter: 1 in - width: 0.25 in
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Product weight	0.1 lb(US)

Environment

Ambient air temperature for operation	-10...185 °F
Ambient air temperature for storage	-10...185 °F
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21494 - 9007 ARMS FOR FT,T
Discount Schedule	DS1
GTIN	00785901816928
Nbr. of units in pkg.	1
Package weight(Lbs)	0.28000000000000003
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------