



Price* : 230.00 USD



9007C52B2WMA31 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Body type	Compact plug-in
Device short name	C
Series name	Heavy duty

Complementary

Line Rated Current	10 A
AWG gauge	AWG 22...AWG 12
Body material	Zinc alloy
Cable entry	0.5 in NPT conduit entry
Contact code designation	A600 Q600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	90 °
Pilot light	Without pilot lamp
Specificity of operator	Standard pre-travel
Switch actuation	CW and CCW
Tilting angle	10 °
Torque value	4 lbf.in
Tripping angle	4 °

Environment

Ambient air temperature for operation	-20...185 °F
NEMA degree of protection	NEMA 1/2/4/6/6P/12/13
Product certifications	UL listed file E42259 CCN NKCR CE CSA LR25490 class 3211 03

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901161400
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------