



Price* : 194.00 USD



9007C52B2Y140 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Device short name	C
Enclosure type	Compact
Head type	Type C turret head rotary lever
Provided equipment	Receptacle
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Cable entry	0.5 in NPT conduit entry
Contact code designation	Q600 A600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Material	Viton fluorocarbon sealing gasket
Maximum displacement angle	90 °
Pilot light	Without pilot lamp
Specificity of operator	Standard pre-travel
Switch actuation	CW and CCW
Tilting angle	10 °
Torque value	4 lbf.in
Tripping angle	4 °

Environment

Ambient air temperature for operation	-20...185 °F
Product certifications	CSA CE UL listed

Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901176428
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------