

Product availability : Stock - Normally stocked in distribution facility



Price* : 170.00 USD



Main

Range of product	9007
Series name	Heavy duty
Head type	Rotary head
Type of operator	Spring return lever arm (standard pre-travel) (to be ordered separately)
Switch actuation	CW
Cable entry	NPT conduit entry, cable outer diameter: 0.5 in
Contacts type and composition	1 NO/1 NC
Contact operation	Snap action

Complementary

Body material	Zinc alloy
Switch function	SPDT-DB
Contact form	Form Z
Contacts material	Silver alloy (Ag/Ni)
Minimum torque for tripping	4 lbf.in
[Ie] rated operational current	10 A, Q600 10 A, A600
[Ui] rated insulation voltage	<= 600 V
Local signalling	Without
Product certifications	CSA UL listed CE
Provided equipment	Receptacle

Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1

GTIN	00785901500735
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25
Returnability	Y
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1150 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------