

Product data sheet

Characteristics

9007C54B1Y185116

LIMIT SWITCH 600V 10AMP C +OPTIONS

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 362.00 USD



Main

Device short name	C
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Electrical connection	Pre-wired cable 5 STOWA 16 ft
Maximum displacement angle	90 °
Number of connectors	1 white 2 black 3 red 4 orange 1 ground connection green
Specificity of operator	Standard pre-travel
Switch actuation	CCW
Tilting angle	10 °
Torque value	4 lbf.in
Tripping angle	4 °

Environment

Ambient air temperature for operation	-20...185 °F
Product certifications	CE CSA UL listed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov