



Price** : 207.00 USD



Main

Device short name	C
Enclosure type	standard
Head type	Type C turret head rotary lever
Provided equipment	Receptacle
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Cable entry	12.70 mm (0.5 in) NPT conduit entry
Contact code designation	Q600 A600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	90 °
Pilot light	without pilot lamp
Switch actuation	CW and CCW
Tilting angle	45 °
Torque value	0.34 N.m (3 lbf.in)

Environment

Ambient air temperature for operation	-29...85 °C (-20...185 °F)
Product certifications	UL listed CE CSA

Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
----------	-----------------------------

Discount Schedule	DS1
GTIN	00785901761662
Package weight(Lbs)	20.00 oz (566.990 g)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP) and Diisononyl phthalate (DINP) which is known to the State of California to cause Carcinogen + Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------