



Price\* : 280.00 USD



9007C54FY140 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

### Main

Device short name	C
Enclosure type	Standard
Head type	Side plunger head
Provided equipment	Receptacle
Series name	Heavy duty

### Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Cable entry	0.5 in NPT conduit entry
Contact code designation	A600 Q600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Material	Viton fluorocarbon sealing gasket
Operating distance	0.25 inch
Operating force	4 lbf
Operating travel	0.08 in 0.03 in
Pilot light	Without pilot lamp
Switch actuation	Vertical
Type of operator	Side roller plunger

### Environment

Ambient air temperature for operation	0...185 °F
Product certifications	CE CSA UL listed

## Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901718796
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------