

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 357.00 USD



ⓘ Discontinued

9007C54GP6Y1905 has not been replaced. Please contact your customer care center for more information.

### Main

Device short name	C
Series name	Heavy duty

### Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Contact code designation	A600 Q600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Number of connectors	1 orange 2 red 3 white 4 black 1 ground connection green
Operating distance	0.25 inch
Operating force	4 lbf
Operating travel	0.08 in 0.03 in
Pilot light	LED 1 NC contact
Switch actuation	Horizontal
Connector type	Mini 5 pins
Type of operator	Side plunger

### Environment

Ambient air temperature for operation	0...185 °F
Product certifications	CE CSA UL listed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

## Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901463481
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------