

9012GCW3G18H11V1Z18

pressure switch 9012G - adjustable scale - 2 thresholds - 170 to 5600 psig

Price** : 824.00 USD



9012GCW3G18H11V1Z18 has not been replaced.
Please contact your customer care center for more information.

⚠ Discontinued

Main

Range of product	9012G
Pressure sensor type	Electromechanical pressure switch
Pressure sensor name	9012G
Pressure sensor size	5600 psi
Maximum pressure	20000 psi
Contacts type and composition	NC-NO, SPDT-DB, Form Z, snap action, silver nickel contacts
Controlled fluid	Air Non-corrosive liquids Non-corrosive gas Hydraulic oil (-15...250 °F)
Fluid connection type	0.44 inch 20 UNF-2B conforming to UL 508
Pressure switch type of operation	Regulation between 2 thresholds
Scale type	Adjustable differential
Local display	With range scale window

Complementary

Range on decreasing pressure	170...5600 psi
Approx adjustable differential at mid range	289...1260 psi +/- 2.5 % full scale
Terminal block type	4 screw terminals
Electrical connection	1 male connector (mini) 5 pins
Terminal identifier	(3)gnd (2-4)NC (1-5)NO
Electrical circuit type	Control circuit
Local signalling	1 neon (red) AC/DC at 120 V (voltage limits:105...125 V
[In] rated current	0.22 A (Ue = 125 V DC) 3 A (Ue = 120 V AC)
Setting	Internal
Enclosure material	Die cast aluminium alloy 380
Pressure actuator	Piston
Height	6.37 in
Depth	3.11 in

Width	3.5 in
Operating position	Any position
Materials in contact with fluid	Teflon Viton fluorocarbon 440 stainless steel 303 stainless steel
Short-circuit protection	10 A by gL (cartridge) overload and short-circuit protection
Operating rate	<= 120 cyc/mn
Mechanical durability	3000000 cycles
Repeat accuracy	4 %
Product weight	3 lb(US)

Environment

Vibration resistance	2 gn conforming to IEC 68-2-6 (f = 40...150 Hz)
Shock resistance	50 gn conforming to IEC 58-2-27
Standards	CE UL 508 CSA C22.2 No 14
Product certifications	CE CSA LR25490 class 3211 03 UL listed file E12158 CCN NKPZ and CCN NTHT
NEMA degree of protection	NEMA 4/4X/13 conforming to UL 50
Ambient air temperature for operation	-10...185 °F

Ordering and shipping details

Category	21522 - 9012 G INDUSTRIAL PRESSURE SWITCHES
Discount Schedule	CP7G
Nbr. of units in pkg.	1
Package weight(Lbs)	3
Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------