

9012GGW1G17H11

pressure switch 9012G - adjustable scale - 2 thresholds - 0 to 75 psig



Price* : 905.00 USD



ⓘ Discontinued

9012GGW1G17H11 has not been replaced. Please contact your customer care center for more information.

Main

Range of product	9012G
Pressure sensor type	Electromechanical pressure switch
Pressure sensor name	9012G
Pressure sensor size	75 psi
Maximum pressure	100 psi
Contacts type and composition	NC-NO, SPDT-DB, Form Z, snap action, silver nickel contacts
Controlled fluid	Air Hydraulic oil (-40...250 °F) Non-corrosive liquids Non-corrosive gas
Fluid connection type	0.25 inch 18 NPTF conforming to UL 508
Pressure switch type of operation	Monitors the difference between 2 thresholds
Scale type	Adjustable differential
Local display	Without

Complementary

Range on decreasing pressure	0...75 psi
Approx adjustable differential at mid range	0.8...2 psi increasing 0.25...10 psi decreasing +/- 2.5 % full scale
Terminal block type	4 screw terminals
Electrical connection	1 male connector (mini) 5 pins
Terminal identifier	(3)Gnd (1-5)NC (2-4)NO
Electrical circuit type	Control circuit
Local signalling	1 neon (clear) AC/DC at 120 V (voltage limits:105...125 V)
[In] rated current	0.22 A (Ue = 125 V DC) 3 A (Ue = 120 V AC)
Setting	Internal

Enclosure material	Die cast aluminium alloy 380
Pressure actuator	Diaphragm (nitrile (Buna-N))
Height	8.02 in
Depth	4.56 in
Width	5.05 in
Operating position	Any position
Materials in contact with fluid	Zinc plated steel Nitrile (Buna-N)
Short-circuit protection	10 A by gL (cartridge) overload and short-circuit protection
Operating rate	<= 120 cyc/mn
Mechanical durability	5000000 cycles
Repeat accuracy	4 %
Product weight	3 lb(US)

Environment

Vibration resistance	2 gn conforming to IEC 68-2-6 (f = 40...150 Hz)
Shock resistance	50 gn conforming to IEC 58-2-27
Standards	CE UL 508 CSA C22.2 No 14
Product certifications	CE CSA LR25490 class 3211 03 UL listed file E12158 CCN NKPZ and CCN NTHT
NEMA degree of protection	NEMA 4/4X/13 conforming to UL 50
Ambient air temperature for operation	-10...185 °F

Ordering and shipping details

Category	21522 - 9012 G INDUSTRIAL PRESSURE SWITCHES
Discount Schedule	CP7G
GTIN	00785901294443
Nbr. of units in pkg.	1
Package weight(Lbs)	3
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------