

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 25.40 USD



Main

Device short name	FHG
Enclosure type	Standard environment enclosure indoor
Factory modification	Maintained manual cut-out lever (AUTO-OFF)
Product specific application	Control small electrically driven air compressors
Range of product	Square D Pumptrol

Complementary

Adjustable range on rising pressure	70...150 psi
Contact code designation	A600
Depth	2.78 in
Electrical connection	Screw clamp terminal
Fixing mode	By brackets
Fluid connection type	0.25 inch NPT external
Height	2.8 in
Materials in contact with fluid	Nitrile (Buna-N) diaphragm
Maximum pressure	220 psig
Motor power hp	1.5 hp 115 V AC 1 phase 2 hp 115 V AC 3 phases 1 hp 460/575 V AC 3 phases 2 hp 230 V AC 1 phase 3 hp 230 V AC 3 phases
Number of poles	2
Permissible voltage	<= 575 V AC
Pressure actuator	Diaphragm
Pressure setting range	125 psi for off
Product weight	1.13 lb(US)
Scale type	Fixed differential
Switch function	DPST

Width	3.76 in
-------	---------

Environment

Approximate fixed differential	30 psi
NEMA degree of protection	NEMA 1
Product certifications	UL listed file E12158 CCN NKPZ CSA LR25490 class 3211 06

Ordering and shipping details

Category	21533 - 9013 FHG (INDIVIDUAL-DISCOUNT CP7I)
Discount Schedule	CP7I
GTIN	00785901836377
Nbr. of units in pkg.	1
Package weight(Lbs)	1
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------