



Price\* : 26.00 USD



ⓘ Discontinued

9013FHG2J27M1P has not been replaced. Please contact your customer care center for more information.

### Main

Device short name	FHG
Enclosure type	Standard environment enclosure indoor
Factory modification	Maintained manual cut-out lever (AUTO-OFF) 0.06 inch pulsation plug
Product specific application	Control small electrically driven air compressors
Range of product	Square D Pumptrol

### Complementary

Adjustable range on rising pressure	40...100 psi
Contact code designation	A600
Depth	2.78 in
Electrical connection	Screw clamp terminal
Fixing mode	By brackets
Fluid connection type	0.25 inch NPSF internal
Height	2.8 in
Materials in contact with fluid	Nitrile (Buna-N) diaphragm
Maximum pressure	220 psig
Motor power hp	1.5 hp 115 V AC 1 phase 2 hp 115 V AC 3 phases 1 hp 460/575 V AC 3 phases 2 hp 230 V AC 1 phase 3 hp 230 V AC 3 phases
Number of poles	2
Permissible voltage	<= 575 V AC
Pressure actuator	Diaphragm
Pressure setting range	100 psi for off
Product weight	1.13 lb(US)
Scale type	Fixed differential
Switch function	DPST
Width	3.76 in

## Environment

Approximate fixed differential	20 psi
NEMA degree of protection	NEMA 1
Product certifications	UL listed file E12158 CCN NKPZ CSA LR25490 class 3211 06

## Ordering and shipping details

Category	21533 - 9013 FHG (INDIVIDUAL-DISCOUNT CP7I)
Discount Schedule	CP7I
GTIN	00785901775515
Nbr. of units in pkg.	1
Package weight(Lbs)	1
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------