

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 43.10 USD



### Main

Device short name	FHG
Enclosure type	Enclosure standard environment indoor
Factory modification	2-way pressure release valve
Product specific application	Control small electrically driven air compressors
Range of product	Square D Pumptrol

### Complementary

Adjustable range on rising pressure	100...200 psi
Approximate fixed differential	35 psi
Contact code designation	A600
Depth	2.78 in
Electrical connection	Screw clamp terminal
Fixing mode	By brackets
Fluid connection type	0.25 inch NPSF internal
Height	2.8 in
Materials in contact with fluid	Nitrile (Buna-N) diaphragm
Maximum pressure	220 psig
Motor power hp	1 hp 460/575 V AC 3 phases 3 hp 115 V AC 3 phases 2 hp 115 V AC 1 phase 3 hp 230 V AC 1 phase 5 hp 230 V AC 3 phases
Number of poles	2
Permissible voltage	<= 575 V AC
Pressure actuator	Diaphragm
Pressure setting range	175 psi off
Product weight	1.13 lb(US)
Scale type	Fixed differential

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Switch function	DPST
Width	3.76 in

### Environment

NEMA degree of protection	NEMA 1
Product certifications	UL listed file E12158 CCN NKPZ CSA LR25490 class 3211 06

### Ordering and shipping details

Category	21533 - 9013 FHG (INDIVIDUAL-DISCOUNT CP7I)
Discount Schedule	CP7I
GTIN	00785901051503
Nbr. of units in pkg.	1
Package weight(Lbs)	1
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <b>Will not be compliant</b>
REACH	Reference not containing SVHC above the threshold <b>Reference not containing SVHC above the threshold</b>
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------