

# 9013GHG3S126J62

## PRESSURE SWITCH 575VAC 5HP G +OPTIONS

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 74.00 USD



### Main

Device short name	G
Enclosure type	Standard environment enclosure indoor
Product specific application	Control electrically driven water pumps and air compressors
Range of product	Square D Pumptrol
Switch application	Standard

### Complementary

Adjustable range on rising pressure	65...200 psi
Approximate adjustable differential	20...40 psi
Depth	3.68 in
Electrical connection	Screw clamp terminal
Fixing mode	By brackets
Fluid connection type	0.375 inch NPSF internal
Height	5.72 in
Material	Zinc plated steel flange
Materials in contact with fluid	Nitrile (Buna-N) diaphragm
Maximum pressure	300 psig
Motor power hp	3 hp 115 V AC 3 phases 5 hp 460/575 V AC 3 phases 5 hp 460/575 V AC 1 phase 2 hp 115 V AC 1 phase 3 hp 230 V AC 1 phase 5 hp 230 V AC 3 phases
Number of poles	2
Permissible voltage	<= 575 V AC
Pressure actuator	Diaphragm
Pressure setting range	140...175 psi

Product weight	2.25 lb(US)
Range on decreasing pressure	40...170 psi
Scale type	Adjustable differential
Switch function	DPST
Width	3.44 in

## Environment

NEMA degree of protection	NEMA 1
Product certifications	UL listed file E12158 CCN NKPZ CSA file LR25490

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <b>Will not be compliant</b>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------