

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 359.00 USD



## Main

Range of product	Square D Pumptrol
Product or component type	Float switch
Device application	Closed tank
Device short name	9037H
Product specific application	Liquid level control
Electrical circuit type	Power circuit
Quantity per set	Set of 1
Type of packing	Individual

## Complementary

Product destination	For closed tank
Device mounting	Screw-in bushing
Cable entry number	2 conduit entries for 3/4"-14 NPT UL 508
Contacts type and composition	2 NC snap action DPST-DB Form YY
Controlled fluid	Fresh water @ specific gravity of 0.85 in or higher 0...250 °F Sea water @ specific gravity of 0.85 in or higher 0...250 °F Hydraulic oil @ specific gravity of 0.85 in or higher 0...250 °F Corrosive fluid @ specific gravity of 0.85 in or higher 0...250 °F
Motor power kW	1.5 kW 2 hp @ 115 V AC 1 phase 2.2 kW 3 hp @ 115 V AC 3 phases 2.2 kW 3 hp @ 230 V AC 1 phase 3.7 kW 5 hp @ 230 V AC 3 phases 0.75 kW 1 hp @ 460 V AC 3 phases 0.75 kW 1 hp @ 475 V AC 3 phases 0.18 kW 0.25 hp @ 32 V DC 0.37 kW 0.5 hp @ 115 V DC 0.37 kW 0.5 hp @ 230 V DC
Electrical connection	Screw-clamp terminals 10 AWG
Contact operation	Contacts close on liquid rise

Float movement	6...11.5 in adjustable
Float position	Left
Float rod angle	90° (offset)
Short-circuit protection	Cartridge fuse gG
Local signalling	With external pointer
Materials in contact with fluid	Cast iron Viton 316 stainless steel Yellow brass 304 stainless steel
Enclosure material	Cast aluminium
Operating position	Vertical position only
Electrical durability	100 cycles @ 60 cyc/mn
Mechanical durability	300 cycles
Terminal block type	4 terminals
Operating rate	60 cyc/mn
[Ui] rated insulation voltage	575 V UL 508
Terminals description ISO n°1	Line-load-load-line
Factory modification	Omit float
Kit composition	Float Rod Float switch

## Environment

Standards	CE UL 508
Ambient air temperature for operation	-22...220 °F
Ambient air temperature for storage	-22...220 °F
NEMA degree of protection	NEMA 7/9 UL 698
Product certifications	UL listed file E12443 CSA file LR26817

## Ordering and shipping details

Category	21601 - 9037,9038 COMMERCIAL FLOAT SWITCHES
Discount Schedule	CP7G
GTIN	00785901122807
Nbr. of units in pkg.	1
Package weight(Lbs)	11
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <a href="#">Will not be compliant</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- Substance 2	Di-isodecyl phthalate (DIDP) which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------