


9038AW1N4

mech alternator - open tank - NEMA 4 - pedestal
mounted - 4 NC DPST-DB contacts

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 632.00 USD



Main

Range of product	Square D Pumptrol
Product or component type	Mechanical alternator
Device application	Open tank
Device short name	9038A
Product specific application	Mechanically alternating the operation of two pumps or motors
Electrical circuit type	Power circuit
Quantity per set	Set of 1
Type of packing	Individual

Complementary

Product destination	For open tank
Device mounting	Pedestal
Cable entry number	2 conduit entries for 3/4"-14 NPT UL 508
Contacts type and composition	4 NC snap action DPST-DB Form YY
Controlled fluid	Fresh water @ specific gravity of 0.85 in or higher Sea water @ specific gravity of 0.85 in or higher Hydraulic oil @ specific gravity of 0.85 in or higher Corrosive fluid @ specific gravity of 0.85 in or higher
Motor power kW	1.5 kW 2 hp @ 115 V AC 1 phase 2.2 kW 3 hp @ 115 V AC 3 phases 2.2 kW 3 hp @ 230 V AC 1 phase 3.7 kW 5 hp @ 230 V AC 3 phases 0.75 kW 1 hp @ 460 V AC 3 phases 0.75 kW 1 hp @ 475 V AC 3 phases 0.18 kW 0.25 hp @ 32 V DC 0.37 kW 0.5 hp @ 115 V DC 0.37 kW 0.5 hp @ 230 V DC
Electrical connection	Screw-clamp terminals 10 AWG
Contact operation	Contacts close on liquid rise

Float movement	Variable adjustable
Float position	Any
Float rod angle	Vertical
Short-circuit protection	Cartridge fuse gG
Local signalling	Without
Enclosure material	Cast aluminium
Operating position	Vertical position only
Electrical durability	100 cycles @ 60 cyc/mn
Mechanical durability	300 cycles
Terminal block type	8 terminals
Operating rate	60 cyc/mn
[U] rated insulation voltage	575 V UL 508
Terminals description ISO n°1	Line-load-load-line
Factory modification	Two-level non-alternating unit
Kit composition	Float switch Rod and float are to be chosen in accessories

Environment

Standards	CE UL 508
Ambient air temperature for operation	-22...220 °F
Ambient air temperature for storage	-22...220 °F
NEMA degree of protection	NEMA 4 UL 50
Product certifications	UL listed file E12158 CSA file LR25490

Ordering and shipping details

Category	21601 - 9037,9038 COMMERCIAL FLOAT SWITCHES
Discount Schedule	CP7G
GTIN	00785901476122
Nbr. of units in pkg.	1
Package weight(Lbs)	16
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------