

9038CW32LZ20

FLOAT SWITCH 575VAC 1HP TYPE C +OPTIONS

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 785.00 USD



Main

Device short name	C
Enclosure type	Dust and damp proof weatherproof enclosure indoor/outdoor
Product specific application	Condensation pump
Switch application	Standard

Complementary

Electrical connection	Screw clamp terminal
Float movement	6.5...13 in
Float position	Left
Material	Stainless steel float/rod Nitrile (Buna-N) seal ring
Motor power hp	3 hp at 230 V AC for 3 phases 1 hp at 460/575 V AC for 3 phases 2 hp at 115 V AC for 1 phase 3 hp at 115 V AC for 3 phases 5 hp at 230 V AC for 1 phase
Mounting support	Flange
Number of poles	2
Permissible voltage	<= 575 V AC
Switch function	DPST

Environment

NEMA degree of protection	NEMA 4
---------------------------	--------

Ordering and shipping details

Category	21601 - 9037,9038 COMMERCIAL FLOAT SWITCHES
Discount Schedule	CP7G

GTIN	00785901456964
Nbr. of units in pkg.	1
Package weight(Lbs)	21.449999999999999
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - Substance 2	Di-isodecyl phthalate (DIDP) which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov