

Product data sheet

Specifications

SQUARE D



Pneumatic Timer, on and off delay, 0.1 to 60 seconds, 24 VAC 60 Hz, SPDT

9050AO110DEV01

Discontinued on: Oct 11, 2019

End-of-service on: Jan 27, 2022

Discontinued

Main

| | |
|-------------------|-----------------------------------|
| Product Range | 9050A/H |
| Product Type | Timer |
| Timing Mode | On-delay and off-delay |
| Timing Range | 0.1 s...1 min |
| Switch Function | SPDT |
| Coil Voltage | 24 V AC 60 Hz |
| Contact Operation | Time delayed 1 NO + 1 NC per head |
| Current Rating | 15 A |

Complementary

| | |
|---------------------------|---------------------------------------|
| Maximum Switching Voltage | 600 V AC |
| Electrical Connection | Screw-clamp terminals |
| Reset Response Time | 29 ms - on-delay 27 ms - off-delay |
| Mounting Support | Panel |

Environment

| | |
|---|--------------------------|
| Ambient Temperature Range - Operational | 68...104 °F (20...40 °C) |
| Certifications | UL Listed CSA |
| Height | 2.64 in (67 mm) |
| Width | 5.67 in (144 mm) |
| Depth | 4.37 in (111 mm) |

Ordering and shipping details

| | |
|-------------------|---|
| Category | 21631-9050 A ONE MINUTE PNEUMATIC TIMER |
| Discount Schedule | CP1 |
| Gtin | 785901592174 |
| Returnability | No |
| Country Of Origin | US |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|