

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 818.00 USD



### Main

Product range	9050A/H
Product type	Timer
Timing mode	On-delay and off-delay
Timing range	0.1 s...1 min
Switch function	SPDT
Coil voltage	110 V AC 50 Hz 120 V AC 60 Hz
Contact operation	Time delayed 1 NO + 1 NC per head
Line Rated Current	15 A

### Complementary

Maximum switching voltage	600 V AC
Electrical connection	Screw-clamp terminals
Reset response time	29 ms - on-delay 27 ms - off-delay
Mounting support	Panel

### Environment

Ambient temperature range - operational	68...104 °F
Certifications	CSA UL listed
Height	2.64 in (67 mm)
Width	5.67 in (144 mm)
Depth	4.37 in (111 mm)

## Ordering and shipping details

Category	21631 - 9050 A ONE MINUTE PNEUMATIC TIMER
Discount Schedule	CP1
GTIN	00785901868026
Nbr. of units in pkg.	1
Package weight(Lbs)	2.3999999999999999
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1444 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------