

Product data sheet

Specifications

SQUARE D



Pneumatic Timer, on and off delay,
0.1 to 60 seconds, 220/240 VAC
50/60 Hz, SPDT

9050AO110DEV03

! Discontinued on: Oct 11, 2019

! End-of-service on: Jan 27, 2022

! Discontinued

Main

Product Range	9050A/H
Product Type	Timer
Timing Mode	On-delay and off-delay
Timing Range	0.1 s...1 min
Switch Function	SPDT
Coil Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Contact Operation	Time delayed 1 NO + 1 NC per head
Current Rating	15 A

Complementary

Maximum Switching Voltage	600 V AC
Electrical Connection	Screw-clamp terminals
Reset Response Time	29 ms - on-delay 27 ms - off-delay
Mounting Support	Panel

Environment

Ambient Temperature Range - Operational	68...104 °F (20...40 °C)
Certifications	CSA UL Listed
Height	2.64 in (67 mm)
Width	5.67 in (144 mm)
Depth	4.37 in (111 mm)

Ordering and shipping details

Category	21631-9050 A ONE MINUTE PNEUMATIC TIMER
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months