

# Product data sheet

Specifications



## Pneumatic Timer Special, off delay, 440/480 VAC 50/60 Hz

9050AO11ES1V06

⚠ Discontinued on: Oct 11, 2019

⚠ End-of-service on: Jan 27, 2022

⚠ Discontinued

### Main

Range	9050A/H
Product	Timer
Current Rating	15 A
Contact Arrangement	SPDT
Contact Configuration	Time delayed 1 NO + 1 NC Instantaneous 1 NO + 1 NC
Operating Temperature Range	68...104 °F (20...40 °C)
Voltage Rating	600 V AC
Mounting Type	Panel
Electrical Connection	Screw-clamp terminals
Certifications	CSA UL Listed
Timing Mode	On-delay
Timing Range	0.1 s...1 min
Reset Response Time	29 ms - on-delay 27 ms - off-delay

### Ordering and shipping details

Category	21631-9050 A ONE MINUTE PNEUMATIC TIMER
Discount Schedule	CP1
Returnability	No
Country Of Origin	US

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.