

Product data sheet

Specifications

SQUARE D



Pneumatic Timer, on delay, 0.1 to 60 seconds, 550/600 VAC 50/60 Hz, timed and instantaneous

9050AO11EV07

! Discontinued

Main

Product Range	9050A/H
Product Type	Timer
Timing Mode	On-delay
Timing Range	0.1 s...1 min
Switch Function	SPDT
Coil Voltage	600 V AC 60 Hz 550 V AC 50 Hz
Contact Operation	Time delayed 1 NO + 1 NC Instantaneous 1 NO + 1 NC
Current Rating	15 A

Complementary

Maximum Switching Voltage	600 V AC
Electrical Connection	Screw-clamp terminals
Reset Response Time	29 ms - on-delay 27 ms - off-delay
Mounting Support	Panel

Environment

Ambient Temperature Range - Operational	68...104 °F (20...40 °C)
Certifications	UL Listed CSA
Height	2.64 in (67 mm)
Width	4.02 in (102 mm)
Depth	4.37 in (111 mm)

Ordering and shipping details

Category	21631-9050 A ONE MINUTE PNEUMATIC TIMER
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.54 in (6.452 cm)
Package 1 Width	6.45 in (16.387 cm)
Package 1 Length	1.00 in (2.54 cm)
Package 1 Weight	34.77 oz (985.792 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov