


9050AO12DV06

Pneumatic Timer - off delay - 0.1-60 seconds -
480VAC - timed and instantaneous



Price** : 675.00 USD



9050AO12DV06 has not been replaced. Please contact your customer care center for more information.

Main

Product range	9050A/H
Product type	Timer
Timing mode	Off-delay
Timing range	0.1 s...1 min
Switch function	SPDT
Coil voltage	440 V AC 50 Hz 480 V AC 60 Hz
Contact operation	Time delayed 1 NO + 1 NC Instantaneous 2 NO + 2 NC
Line Rated Current	15 A

Complementary

Maximum switching voltage	600 V AC
Electrical connection	Screw-clamp terminals
Reset response time	29 ms - on-delay 27 ms - off-delay
Mounting support	Panel

Environment

Ambient temperature range - operational	68...104 °F
Certifications	CSA UL listed
Height	2.64 in (67 mm)
Width	4.02 in (102 mm)
Depth	4.37 in (111 mm)

Ordering and shipping details

Category	21631 - 9050 A ONE MINUTE PNEUMATIC TIMER
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	2.1800000000000002
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------