




Price* : 549.00 USD



9050AO20DV04 has not been replaced. Please contact your customer care center for more information.

Main

Product range	9050A/H
Product type	Timer
Timing mode	Off-delay
Timing range	0.1 s...1 min
Switch function	DPDT
Coil voltage	277 V AC 60 Hz
Contact operation	Time delayed 2 NO + 2 NC
Line Rated Current	10 A

Complementary

Maximum switching voltage	600 V AC
Electrical connection	Screw-clamp terminals
Reset response time	29 ms - on-delay 27 ms - off-delay
Mounting support	Panel

Environment

Ambient temperature range - operational	68...104 °F
Certifications	CSA UL listed
Height	2.64 in (67 mm)
Width	4.02 in (102 mm)
Depth	4.37 in (111 mm)

Ordering and shipping details

Category	21631 - 9050 A ONE MINUTE PNEUMATIC TIMER
----------	---

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	2.0699999999999998
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------