



Price\*\* : 675.00 USD



9050AO21DV01 has not been replaced. Please contact your customer care center for more information.

## Main

Product range	9050A/H
Product type	Timer
Timing mode	Off-delay
Timing range	0.1 s...1 min
Switch function	DPDT
Coil voltage	24 V AC 60 Hz
Contact operation	Instantaneous 1 NO + 1 NC Time delayed 2 NO + 2 NC
Line Rated Current	10 A

## Complementary

Maximum switching voltage	600 V AC
Electrical connection	Screw-clamp terminals
Reset response time	29 ms - on-delay 27 ms - off-delay
Mounting support	Panel

## Environment

Ambient temperature range - operational	68...104 °F
Certifications	CSA UL listed
Height	2.64 in (67 mm)
Width	4.02 in (102 mm)
Depth	4.37 in (111 mm)

## Ordering and shipping details

Category	21631 - 9050 A ONE MINUTE PNEUMATIC TIMER
----------	-------------------------------------------

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	2.0699999999999998
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------