

# Product data sheet

Specifications

SQUARE D



Pneumatic Timer, off delay, 0.1 to 60 seconds, 220/240 VAC 50/60 Hz, timed and instantaneous

9050AO22DV03

Discontinued on: Oct 11, 2019

End-of-service on: Jan 27, 2022

Discontinued

## Main

Product Range	9050A/H
Product Type	Timer
Timing Mode	Off-delay
Timing Range	0.1 s...1 min
Switch Function	DPDT
Coil Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Contact Operation	Instantaneous 2 NO + 2 NC Time delayed 2 NO + 2 NC
Current Rating	10 A

## Complementary

Maximum Switching Voltage	600 V AC
Electrical Connection	Screw-clamp terminals
Reset Response Time	29 ms - on-delay 27 ms - off-delay
Mounting Support	Panel

## Environment

Ambient Temperature Range - Operational	68...104 °F (20...40 °C)
Certifications	CSA UL Listed
Height	2.64 in (67 mm)
Width	4.02 in (102 mm)
Depth	4.37 in (111 mm)

## Ordering and shipping details

Category	21631-9050 A ONE MINUTE PNEUMATIC TIMER
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# Contractual warranty

Warranty	18 months
----------	-----------